



MMU2S Buffer vertical mount

 Lars Kollin

[VIEW IN BROWSER](#)

updated 10. 10. 2022 | published 10. 10. 2022

Summary

Mount the MMU2 buffer vertically to a board

[3D Printers](#) > [Accessories](#)

Tags: mmu2

My wall cupboard printer enclosure does not allow a setup for the mmu2s buffer as recommended by prusa. I just do not have enough depth in that cupboard, but I do have space below the printer. I use an IKEA store rack/shelf system (ALGOT) and so I made a vertical mount for the buffer fitting for these IKEA shelves which are 18mm thick.

All you need is a rubberband to keep the buffer clamped between the mounts and voilà vertical buffer happiness. The buffer still works as intended, the orientation does not affect the function at all.

Model files



[mmu_buffer_holder_b.stl](#)



mmu2_mount.blend

License ©

This work is licensed under a
Creative Commons (International License)



Public Domain

- ✓ | Sharing without ATTRIBUTION
- ✓ | Remix Culture allowed
- ✓ | Commercial Use
- ✓ | Free Cultural Works
- ✓ | Meets Open Definition