

Mzuzah Casting mold



idona

[VIEW IN BROWSER](#)

updated 7. 1. 2024 | published 7. 1. 2024

Summary

Mzuzah Casting mold - use tpu to print the mold and apoxy to cast it.



14.87 hrs



2 pcs



0.15 mm



0.40 mm



Flex



88 g




Prusa
MK3/S/S+

[Household](#) > [Home Decor](#)

Tags: [epoxy](#) [molding](#) [mold](#) [resin](#) [molds](#) [mezuzah](#)
[mzuzah](#)

Mzuzah Casting mold - use tpu to print the mold and apoxy to cast it.

Model files



mzuzah-casting-mold.stl

Print files



mzuzah-casting-mold-_04n_015mm_flex_mk3s_14h52m.gcode

⚙ Flex 📏 0.40 mm 📏 0.15 mm ⌚ 14.87 hrs ⚖ 88 g 🖨 Prusa MK3/S/S+

📄 infill 15%



mzuzah-casting-mold_04n_015mm_flex_mk3s_15h55m.gcode

⚙ Flex 📏 0.40 mm 📏 0.15 mm ⌚ 15.91 hrs ⚖ 94 g 🖨 Prusa MK3/S/S+

📄 infill 30%

License ©



This work is licensed under a
[Creative Commons \(4.0 International License\)](#)

Attribution—Noncommercial—Share Alike

- ✖ | Sharing without ATTRIBUTION
- ✓ | Remix Culture allowed
- ✖ | Commercial Use
- ✖ | Free Cultural Works
- ✖ | Meets Open Definition