



Vesa 100 distance plates



Boogie

[VIEW IN BROWSER](#)

updated 20. 8. 2021 | published 25. 7. 2021

Summary

Distance plates for vesa 100 mount



6.71 hrs



2 pcs



0.15 mm



0.40 mm



PLA
PET



97 g



Prusa
MK3/S/S+

[Gadgets](#) > [Computers](#)

Tags: [mount](#) [distance](#) [100](#) [vesa](#)

Distance plates for vesa 100 mount

Model files



vesa_100_distance_plate1.stl

☐ Thickness 5 mm, hole diameter 5 mm



vesa_100_distance_plate2.stl

☐ Thickness 6 mm, hole diameter 4 mm

Print files



vesa_100_distance_plate1_015mm_petg_mk3s_2h59m.gcode

🌀 PET 🌀 0.40 mm ≡ 0.15 mm ⌚ 2.98 hrs ⚖️ 43 g 🖨️ Prusa MK3/S/S+

☐ Thickness 5 mm, hole diameter 5 mm



vesa-100_distance_plate2_015mm_pla_mk3s_3h44m.gcode

🌀 PLA 🌀 0.40 mm ≡ 0.15 mm ⌚ 3.73 hrs ⚖️ 54 g 🖨️ Prusa MK3/S/S+

☐ Thickness 6 mm, hole diameter 4 mm

License ©

This work is licensed under a
[Creative Commons \(4.0 International License\)](#)



Attribution

- ✗ | Sharing without ATTRIBUTION
- ✓ | Remix Culture allowed
- ✓ | Commercial Use
- ✓ | Free Cultural Works
- ✓ | Meets Open Definition