



6mm OD 3mm ID to 4mm OD 2.5mm ID PTFE tube reducer eSun eBox Lite to PRUSA

 **midnight**

[VIEW IN BROWSER](#)

updated 1. 4. 2024 | published 1. 4. 2024

Summary

Adapt a 4mm OD 2.5mm ID PTFE tube to 4mm OD 2.5mm ID.

[3D Printers](#) > [Prusa Parts & Upgrades](#)

Tags: [filament](#) [filamentguide](#) [reducer](#) [filamentdrybox](#)
[ptfecoupler](#)

Printed on an MK4 0.15 QUALITY profile (with a brim to ensure bed adhesion).

Uses a friction fit. Could scale to 99% or 98% if too loose or scale up to 101% or 102% if too tight.

This remix is based on



6mm to 4mm OD PTFE tube reducer eSun eBox Lite to bambulab X1C X1 P1P

by E Sands

Model files



6mm-od-3mm-id-to-4mm-od-25mm-id-filament-tube-reduc... .stl



6mm-od-3mm-id-to-4mm-od-25mm-id-filament-tube-reduc... .stl

License

This work is licensed under a
[Creative Commons \(4.0 International License\)](#)



Attribution

-
- ✗ | Sharing without ATTRIBUTION
 - ✓ | Remix Culture allowed
 - ✓ | Commercial Use
 - ✓ | Free Cultural Works
 - ✓ | Meets Open Definition