



## ProxMark3 Easy Case



Nadav

[VIEW IN BROWSER](#)

updated 27. 7. 2024 | published 27. 7. 2024

### Summary

ProxMark3 Easy Case for Mounting on the Wall



14.50 hrs



2 pcs



0.10 mm



0.40 mm



PLA



69 g



Artillery  
Genius

[Hobby & Makers](#) > [Electronics](#)

Tags: [proxmark3](#) [proxmark3easy](#)

This model is supposed to expand the use of the ProxMark3 Easy by making it more common in your work environment.

I need to say, before installing the ProxMark3 Easy on the model, you should first remove the middle layer of the ProxMark, Don't worry this layer's only purpose is to be a gap between the first and the last layer and has no other functionality.

P.S. You need 4 m2 \* 0.4mm nuts to get rid of the middle layer of the ProxMark  
enjoy😊

## Model ʒles



proxmark3-easy-case-v4.stl



proxmark3-easy-button-v2.stl

## Print ʒles



ag\_proxmark3-case-v4.gcode

⚙️ PLA ⚙️ 0.40 mm ⚙️ 0.10 mm ⌚ 14.50 hrs ⚖️ 69 g



ag\_proxmark3-easy-button-v2.gcode

⚙️ PLA ⚙️ 0.40 mm ⚙️ 0.10 mm ⌚ 0.17 hrs ⚖️ 1 g

## License Ɔ

This work is licensed under a  
[Creative Commons \(International License\)](#)



[Public Domain](#)

- ✓ | Sharing without ATTRIBUTION
- ✓ | Remix Culture allowed
- ✓ | Commercial Use
- ✓ | Free Cultural Works
- ✓ | Meets Open Definition

